



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24H20BLP 24X20X8 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | A24H20BLP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Continuous Hinge Enclosure With Clamps LP Type 4, 24X20X8, Gray, Mild Steel |
| Weight per unit | 38.0 (lbs/each) |
| Product Category | Nema Types 4 & 12 Metallic Enc |

Features

| | |
|-----------|------------|
| ip rating | IP66 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 24 |
| Size | 24.00x20.00x8.00 in |
| Width | 20 |

Descriptions

| | |
|------------------------|--|
| Description | 24X20X8 N4 CH CLMP CVR |
| extra long description | NVENT HOF A24H20BLP Type 4 Encl. 24 |
| Features | These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications. |
| Long Description | Continuous Hinge Enclosure with Clamps LP Type 4, 24x20x8, Gray, Mild Steel |
| Product Type | Type 4 Encl. 24.00X20.00X8.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510244408 |
| Manufacturers Part Number | A24H20BLP |
| UPC | 783510244408 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 38 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Controls and Drives |
| nema rating | 12 Indoor, dust-resistant |