



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **A30H2408SSLP 30X24X8" N4X SS4 CH CLMP CVR**

*Hoffman Enclosures, Inc.*

Catalog Number	A30H2408SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 30X24X8, Brushed, SS304
Weight per unit	59.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### **Features**

ip rating	IP66
Material	Stainless Steel 304

### **Material, Color, and Finish**

Color	Unpainted
Finish	Brushed #4

### **Dimensions and Weight**

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

### **Descriptions**

Description	30X24X8" N4X SS4 CH CLMP CVR
extra long description	NVENT HOF A30H2408SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 30x24x8, Brushed, SS304
Product Type	Stainless Encl. 30.00X24.00X8.

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510241100
Manufacturers Part Number	A30H2408SSLP
UPC	783510241100

### **Taxonomies, Classifications, and Categories**

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	59

## Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant