



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A30H24BLP 30X24X8 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A30H24BLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 30X24X8, Gray, Mild Steel
Weight per unit	58.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

ip rating	IP66
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

Descriptions

Description	30X24X8 N4 CH CLMP CVR
extra long description	NVENT HOF A30H24BLP Type 4 Encl. 30
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 30x24x8, Gray, Mild Steel
Product Type	Type 4 Encl. 30.00X24.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510244705
Manufacturers Part Number	A30H24BLP
UPC	783510244705

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	58

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12 Indoor, dust-resistant