



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A363612LP 36X36X12 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A363612LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 12, 36X36X12, Gray, Mild Steel
Weight per unit	103.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP65
Material	MILD STEEL

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	12
Height	36
Size	36.00x36.00x12.00 in
Width	36

Descriptions

Description	36X36X12 N12 CH CLMP CVR
extra long description	NVENT HOF A363612LP Enclosure 36.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 12, 36x36x12, Gray, Mild Steel
Product Type	Enclosure 36.00X36.00X12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510279509
Manufacturers Part Number	A363612LP
UPC	783510279509

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	103



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12 Indoor, dust-resistant