



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **A36H3012GQRLP 36.25X30.25X12 N4X FG QR HC** *Hoffman Enclosures, Inc.*

Catalog Number	A36H3012GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 36.25X30.25X12.00, Gray, Fiberglass
Weight per unit	52.9 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### **Features**

ip rating	IP66
Material	Fiberglass

### **Material, Color, and Finish**

Color	Gray
Finish	Smooth Matte

### **Dimensions and Weight**

Depth	12
Height	36.25
Size	36.25x30.25x12.00 in
Width	30.25

### **Descriptions**

Description	36.25X30.25X12 N4X FG QR HC
extra long description	NVENT HOF A36H3012GQRLP Enclosure 3
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 36.25x30.25x12.00, Gray, Fiberglass
Product Type	Enclosure 36.25X30.25X12.00

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510226602
Manufacturers Part Number	A36H3012GQRLP
UPC	783510226602

### **Taxonomies, Classifications, and Categories**

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	52.9

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant