



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A4424RT 4X4X24 N3R SC Wire Trough

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | A4424RT |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wiring Trough Nema Type 3R, 4.00X4.00X24.00, Gray, Steel |
| Weight per unit | 9.3 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

Features

| | |
|-----------|------------|
| ip rating | IP32 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Galvanized |

Dimensions and Weight

| | |
|-------|--------------------|
| Depth | 24 |
| Size | 4.00x4.00x24.00 in |
| Width | 4 |

Descriptions

| | |
|------------------------|--|
| Description | 4X4X24 N3R SC WIRE TROUGH |
| extra long description | NVENT HOF A4424RT Wiring Trough 4.0 |
| Features | Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security. |
| Long Description | Wiring Trough NEMA Type 3R, 4.00x4.00x24.00, Gray, Steel |
| Product Type | Wiring Trough 4.00X4.00X24.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510382100 |
| Manufacturers Part Number | A4424RT |
| UPC | 783510382100 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Trough |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 9.29 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Power Distribution |
| nema rating | 3R Weather-resistant, except dust |