



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A4AXFNPG 115V, 50/60HZ, 17/15W, 0.26/0.21a *Hoffman Enclosures, Inc.*

Catalog Number	A4AXFNPG
Manufacturer	Hoffman Enclosures, Inc.
Description	Compact Axial Fan 4-Inch Power Cord, 115VAC 100CFM, Black, Steel
Weight per unit	1.6 (lbs/each)
Product Category	Fans - Industrial & Commercial

Features

amperage rating	.26/.21 A
Blade Size	4.69-inch diameter
flow rate	85/100 CFM max
Material	MILD STEEL
motor type	AC Motor
nominal voltage	115
Voltage Rating	100 - 120 VAC

Material, Color, and Finish

Color	Jet Black
Color Code	RAL 9005
Finish	Powder Coated

Dimensions and Weight

Size	115v 50/60Hz in
------	-----------------

Descriptions

Description	115V,50/60HZ,17/15W,0.26/0.21A
extra long description	NVENT HOF A4AXFNPG 115V,50/60Hz,17/
Features	Compact Cooling Fans are ideal for applications where enclosure space is limited and quiet, reliable cooling is required. Engineered for 50,000 hours of continuous operation without lubrication or service.
Long Description	Compact Axial Fan 4-inch Power Cord, 115VAC 100CFM, Black, Steel
Product Type	115V, 50/60HZ, 17/15W, 0.26/0.21a

Manufacturer Information

Brand	Hoffman Enclosures, Inc.
Manufacturers Part Number	A4AXFNPG

Taxonomies, Classifications, and Categories

Type	Fans and Filter Fans
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.6

Uses, Certifications, and Standards

Application	Datacom and Telecom Equipment; Networking, Storage and Data Center
-------------	--