



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A560MHW 60MIN Twist Timer W/Hold White

Nsi Industries

Catalog Number	A560MHW
Manufacturer	Nsi Industries
Description	Interval Timer 60 Min Hold White
Weight per unit	0.3240 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	60 Minute

Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------

Descriptions

Description	60MIN TWIST TIMER W/HOLD WHITE
extra long description	TORK A560MHW Interval Timer 60 Min
Features	Tork 60 Min Twist Timer w/ Hold In-Wall Time Switch APPLICATIONS: Whole House Fans, Indoor/Outdoor Lighting, Bathroom Fans and Lights, Self Storage. FEATURES: COLOR: White VARIABLE TIMING: Twist knob for time ON setting up to 60 minutes. HOLD FEATURE: Has position for constant ON (Hold). EASY SET : No adjustments. Just wire and go, EASY WIRING: No neutral required. Great for retrofit, Use as single or in multi-gang box with no de-rating. SWITCH TYPE: SPST WALL PLATE: Fits standard or decorator style wall p
Long Description	Interval Timer 60 Min Hold White
Product Type	Interval Timer 60 Min White
Special Features	White 60 Minute With Hold In Wall Time Switch

Manufacturer Information

Brand	NSi
GTIN	00786261151223
Manufacturers Part Number	A560MHW
UPC	786261151223

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Spring Wound In Wall Time Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.324

Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus