



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A6Y1011 90175-Fuse, Form 600

Mersen Fuses

Catalog Number	A6Y1011
Manufacturer	Mersen Fuses
Description	Fuse A6Y 600VAC 500VDC 10A Type 11 Ferrule Amp-Trap®
Weight per unit	0.0500 (lbs/each)
Product Category	Current Limiting

Features

AC Voltage Rating	600
amperage rating	10
connection	Ferrule
DC Voltage Rating	500
interrupt rating	200

Material, Color, and Finish

Body Material	GMG
---------------	-----

Dimensions and Weight

Size	2 x 0.57
------	----------

Descriptions

Description	90175-FUSE,FORM 600
extra long description	Mersen A6Y10-11 Fuse A6Y 600VAC 500
Features	Mersen Form 600 fuses are the original current-limiting fuses, predating all the standards. Their 500V DC rating (through 600A) is a useful feature for special fusing applications. Form 600 fuses provide a high degree of current limitation in AC and DC applications. Types 1 and 3 are dimensionally interchangeable with Class H and K fuses. Types 4 and 5 have unique rejection dimensions and are not interchangeable.
Long Description	Fuse A6Y 600VAC 500VDC 10A Type 11 Ferrule Amp-Trap®
Product Type	Fuse A6Y 600VAC 500VDC 10A Type 11 Ferrule Amp-Trap®
Short Description	90175-FUSE,FORM 600

Manufacturer Information

Brand	Mersen
GTIN	00782001901752
Manufacturers Part Number	A6Y10-11
UPC	782001901752

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	DC Fuses



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.05

Uses, Certifications, and Standards

Mounting	Clip
standard	UL Recognized Component File E60314 DC Tested to UL248-1 (1-600A)