



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AE80BF *Delisted* 80 CFM 1.5 Sones Fan Pack Energy Star

Broan/Nutone LLC

Catalog Number	AE80BF
Manufacturer	Broan/Nutone LLC
Description	Ventilation Fan, Rugged 26 Gauge Galvanized Steel, Ceiling Mount, 120 V Ac @ 60 HZ, 26.9 W, 0.3 A, 80 CFM Air Flow, 60 HZ, Round Duct Shape, 4 In Duct Size, White Polymeric, Polymeric Grill Material, Rectangular Grill Shape, 11-3/8 In (L) X 12 In (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Rectangular Housing Shape, Permanently Lubricated Plug-In Motor, 9-1/4 In Overall Length, 10 In Overall Width, 5-3/4 In Overall Height, 4 In Duct Diameter, Exhaust, 1.41 LB
Weight per unit	22.5 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	80 CFM
Sound Level	1.5 SONES
Ventilation Area	75 Square Foot

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---

Descriptions

Additional Information	Power Rating 26.9 Watt; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 4 per Master Carton
Commodity Description	Exhaust Fans
Description	*DELISTED* 80 CFM 1.5 SONES FAN PACK ENERGY STAR
extra long description	FINISH PACK TYPE; A000HFC FAN HOUSING PACK, BATH AND VENTILATION FAN USED ON; INVENT[TM] BRAND; AIRFLOW RATING 80 CFM; SOUND 1.5 SONES; DUCT SIZE 4 INCH; OVERALL DIMENSION 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT; COLOR WHITE POLYMERIC; APPROVAL UL, UL (CANADA AND USA)

Manufacturer Information

Brand	BROAN
GTIN	00026715236091
Model	Model AE80B
UPC	026715236091

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	22.5

Uses, Certifications, and Standards

Approval	UL (Canada and US), HVI
----------	-------------------------