



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AE80BL 80CFM Fan W/Led Light 1.5 Sones

Broan/Nutone LLC

|                  |   |
|------------------|---|
| Catalog Number   | AE80BL  |
| Manufacturer     | Broan/Nutone LLC  |
| Description      | Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt Voltage Rating; 0.5 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage |
| Weight per unit  | 9.2 (lbs/each)  |
| Product Category | Exhaust Fans  |

### Features

|                  |  |
|------------------|--|
| Air Flow Rate    | 80 CFM                                 |
| Current Rating   | 0.5 Amp                                |
| Duct Shape       | Round                                  |
| Duct Size        | 4 Inch Diameter                        |
| Grill Finish     | White                                  |
| Grill Shape      | Rectangular                            |
| Grill Size       | 11-3/4 Inch Length x 12-1/2 Inch Width |
| Housing Shape    | Rectangular                            |
| Lamp Included    | Yes                                    |
| Lamp Type        | LED                                    |
| Lamp Wattage     | 11 Watt                                |
| Sound Level      | 1.5 SONES                              |
| Ventilation Area | 75 Square Foot (Bathroom)              |
| Voltage Rating   | 120 Volt                               |

### Material, Color, and Finish

|                  |                                  |
|------------------|----------------------------------|
| Grill Material   | Polymeric                        |
| Housing Material | 26 Gauge Rugged Galvanized Steel |

### Dimensions and Weight

|      |   |
|------|---|
| Size | 9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height |
|------|---|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Power Rating 26.9 Watt; Includes Grille, Blower, Dimming Control  |
| Commodity Description  | Exhaust Fans  |
| Description            | 80CFM FAN W/LED LIGHT 1.5 SONES   |
| extra long description | CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; 26 GAUGE RUGGED GALVANIZED STEEL HOUSING MATERIAL; 80 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.5 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT (BATHROOM |
| Long Description       | BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE   |
| Product Type           | Bath Fan and Light  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | BROAN          |
| GTIN                      | 00026715239573 |
| Manufacturers Part Number | AE80BL         |
| UPC                       | 026715239573   |

## Taxonomies, Classifications, and Categories

|                      |                |
|----------------------|----------------|
| Category Description | FANS & HEATERS |
| Type                 | CEILING        |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 9.16 |

## Uses, Certifications, and Standards

|          |         |
|----------|---------|
| Approval | UL, HVI |
|----------|---------|