



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC10 10A 250V 1/4X1-1/4 Rohs Fa Glass Fuse

*Bussmann Fuses*

Catalog Number	AGC10
Manufacturer	Bussmann Fuses
Description	Buss Agc-10 Agc Glass Fuse - 1/4 X
Weight per unit	0.0100 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	10 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

### Descriptions

Description	10A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
Long Description	BUSS AGC-10 AGC GLASS FUSE - 1/4 x
Product Type	Agc Glass Fuse - 1/4 X 1-1/4 - 10 Amp
Special Features	Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703925
Manufacturers Part Number	AGC-10
UPC	051712703925

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

### Availability

Manufacturer Status	Inactive
Status	Inactive

### Packaging

Carton	5
Weight Per each	0.01

### Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA