



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC15 15A 32V 1/4X1-1/4 Rohs Fa Glass Fuse

*Bussmann Fuses*

Catalog Number	AGC15
Manufacturer	Bussmann Fuses
Description	3/10A 125V 3AG - 1/4" X 1-1/4" Glass, Fast Acting Fuse
Weight per unit	0.0070 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	15 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	32 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

### Descriptions

Description	15A 32V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	EFSE AGC-15 BUSS SMALL DIMENSION FU
Long Description	3/10A 125V 3AG - 1/4" x 1-1/4" Glass, Fast Acting Fuse
Product Type	Buss Small Dimension Fuse 5N Auto Pack
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703932
Manufacturers Part Number	AGC-15
UPC	051712703932

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	5
Weight Per each	0.007

### Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA