



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC8 8A 250V 1/4X1-1/4 Rohs Fa Glass Fuse

*Bussmann Fuses*

Catalog Number	AGC8
Manufacturer	Bussmann Fuses
Description	6A 250V 3AG - 1/4" X 1-1/4" Glass, Fast Acting Fuse
Weight per unit	0.0080 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	8 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

### Descriptions

Description	8A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	EFSE AGC-8 BUSS SMALL DIMENSION FUS
Long Description	6A 250V 3AG - 1/4" x 1-1/4" Glass, Fast Acting Fuse
Product Type	Buss Small Dimension Fuse Fast Acting
Special Features	Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703918
Manufacturers Part Number	AGC-8
UPC	051712703918

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	5
Weight Per each	0.008

### Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA