



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGFTR2152W4 TR Gfci 15A WH

*Pass & Seymour/Legrand*

Catalog Number	AGFTR2152W4
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Gfci, 15A White
Weight per unit	0.2925 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Side & Back Wire
Connection Type	Internal Pressure Plates
indoor/outdoor	Indoor
interrupt rating	.025 Second Nominal
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Self-Test, GFCI, Tamper-Resistant
Phase	Single
Poles	2
trip range	4 to 6 mA
Voltage Rating	125

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	2.66
Length	1.82
Width	1.77

### Descriptions

Description	TR GFCI 15A WH
extra long description	ADO AGFTR2152W4 TAMPER-RESISTANT GF
Long Description	TAMPER-RESISTANT GFCI, 15A WHITE
Product Type	Tamper-Resistant Gfci, 15A WH
Special Features	GFCIs protect against serious injury due to electric shock. They are required by National Electrical Code in kitchens and bathrooms



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	legrand
GTIN	00785007052626
Manufacturers Part Number	AGFTR2152-W4
UPC	785007052626

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Tamper-Resistant GFCI Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	4
Weight Per each	0.2925

## Uses, Certifications, and Standards

Application	Residential Outlet
environmental conditions	95% (relative humidity, non-condensing)
Frequency Rating	60Hz
nema rating	15A, GFCI
standard	cULus