



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH6810W AH6810U In Nema 3R Enclosure

Eaton Wiring Devices

Catalog Number	AH6810W
Manufacturer	Eaton Wiring Devices
Description	Eaton Manual Motor Controller, #14-10 Awg, 30A, Wall, 600V, Front Wired, Maintained Contact, Gray, Nema 3R, Enclosure: Copperless Aluminum, Two-Pole, -20-65 C, Single-Phase, Toggle Switch, Copper-Alloy Terminal, Brass Screw, Single-Throw
Weight per unit	3.1 (lbs/each)
Product Category	Definite Purpose Contactors

Features

amperage rating	30A
dimensions	9.3000 IN X 7.0000 IN X 5.9000 IN
Poles	Two-pole
Voltage Rating	600 V

Descriptions

Description	AH6810U IN NEMA 3R ENCLOSURE
extra long description	EWD AH6810W AH6810U in NEMA 3R Encl
Features	Eaton's Arrow Hart manual motor controllers offer compact, industrial-grade designs built to provide safe, reliable motor control performance in even the most rugged environments. They feature high-impact-resistant, glass-filled nylon construction; easy-to-read electrical ratings on rugged steel mounting straps; clear ON/OFF indicators on large, rugged toggles; distinct wire pockets and thick-wall arc barriers to contain strands; and screw-and-clamp or box-lug terminals to meet individual project requireme
Long Description	Eaton manual motor controller, #14-10 AWG, 30A, Wall, 600V, Front wired, Maintained contact, Gray, NEMA 3R, Enclosure: Copperless aluminum, Two-pole, -20-65 C, Single-phase, Toggle switch, Copper-alloy terminal, brass screw, Single-throw
Product Type	AH6810U In Nema 3R Enclosure
Special Features	With NEMA 3R enclosure

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00040893616865
Manufacturers Part Number	AH6810W
UPC	040893616865



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	REVERSING
Type	Manual motor controller

Packaging

Carton	1
Weight Per each	3.05

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
nema rating	3R
Operating Temperature	-20 to 65 °C
standard	cULus Listed,RoHS Compliant,NAFTA