



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AMC5075 1/2" Ez-Lock Assy *Bridgeport Fittings*

Catalog Number	AMC5075
Manufacturer	Bridgeport Fittings
Description	Connector, E-Z Lock, Steel, .565 Inch Throat Opening
Weight per unit	0.1240 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

angle	180
Connector Type	E-Z Lock®
Material	Steel
media	Yes
Number of Conductors	1 Cable

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	1/2
------	-----

Descriptions

Description	1/2" EZ-LOCK ASSY
extra long description	BPT AMC-5075 1/2" E-Z LOCK ASSY
Features	Think Orange: Meet the Steel Spec and Speed the Installation with the EZ-Lock Snap-in Connector.
Long Description	Connector, E-Z Lock, Steel, .565 Inch Throat Opening
Product Type	1/2" E-Z Lock Assy

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747205773
Manufacturers Part Number	AMC-5075
UPC	781747205773

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	25
Package	250
Weight Per each	0.124



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Recommended cable types used to connect steel interlocked, aluminum interlocked and aluminum corrugated metal clad cable, 1/2" FMC to box or enclosure. Insulator rated 105 degree C. Diameter for 10/4 (.62" 0 min) to 6/3 (.803" 0 max)

standard

cULus

Temperature Rating

105°C