



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AMC5075 1/2" Ez-Lock Assy *Bridgeport Fittings*

| | |
|------------------|--|
| Catalog Number | AMC5075 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, E-Z Lock, Steel, .565 Inch Throat Opening |
| Weight per unit | 0.1240 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|----------------------|-----------|
| angle | 180 |
| Connector Type | E-Z Lock® |
| Material | Steel |
| media | Yes |
| Number of Conductors | 1 Cable |

Material, Color, and Finish

| | |
|--------|--------------------|
| Finish | Zinc Electroplated |
|--------|--------------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 1/2 |
|------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 1/2" EZ-LOCK ASSY |
| extra long description | BPT AMC-5075 1/2" E-Z LOCK ASSY |
| Features | Think Orange: Meet the Steel Spec and Speed the Installation with the EZ-Lock Snap-in Connector. |
| Long Description | Connector, E-Z Lock, Steel, .565 Inch Throat Opening |
| Product Type | 1/2" E-Z Lock Assy |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747205773 |
| Manufacturers Part Number | AMC-5075 |
| UPC | 781747205773 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 1/2 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.124 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Recommended cable types used to connect steel interlocked, aluminum interlocked and aluminum corrugated metal clad cable, 1/2" FMC to box or enclosure. Insulator rated 105 degree C. Diameter for 10/4 (.62" 0 min) to 6/3 (.803" 0 max)

standard

cULus

Temperature Rating

105°C