

BURNDY Catalog Number
UPC Number
Description
Status

AMS4/0
 7818102410288
 4/0-6 DUAL RATED SPLICE
 Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.31
Hex Size	5/16
H1	1.09
General	
Number of Screws	2
Product Description	Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-4/0 AWG
Copper Solid Size (Range)	6 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-4/0 AWG
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Splice, Reducer
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

AMS4/0
 7818102410288
 4/0-6 DUAL RATED SPLICE
 Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.31
Hex Size	5/16
H1	1.09
General	
Number of Screws	2
Product Description	Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-4/0 AWG
Copper Solid Size (Range)	6 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-4/0 AWG
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Splice, Reducer
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175