



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



APCH7R *Delisted* Emergency/Exit Combo Remote Capacity

Cooper Lighting Solutions

Catalog Number	APCH7R
Manufacturer	Cooper Lighting Solutions
Description	Polycarbonate Exit Sign, Polycarbonate Material, Single;Double Faces, Red Text Color, 3.6 V DC, 1.31 W @ 120 V;1.68 W @ 277 V, 3-15/16 In Depth, 16-9/16 In Length, 8-1/4 In Height, White, Battery Included, Nickel Cadmium (Nicaid) Battery, 2 Lamps, Led Bulb, 5 Yr;7 Yr (Battery) Warranty, Surface Mount, 2.4 LB
Weight per unit	2.4 (lbs/each)
Product Category	Exit Signs

Features

amperage rating	.09 at 277V
battery	Nickel Cadmium
Fixture Type	Emergency Exit Combination Light
Lamp Type	LED
lumens	N/A

Dimensions and Weight

Size	8.5 IN Length 13.25 IN Width 2.6 IN Height
------	--

Descriptions

Description	EMERGENCY/EXIT COMBO REMOTE CAPACITY
extra long description	CLS APCH7R EXIT, RED, NI-CAD, SELF-

Manufacturer Information

Brand	ALL-PRO EMERGENCY
GTIN	00080083567171
UPC	080083567171

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	LED Exit and Emergency

Packaging

Carton	1
Package	8
Weight Per each	2.4

Uses, Certifications, and Standards

Mounting	Ceiling and Surface
standard	UL/cUL Listed - Damp Location