



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## APS11 1/0 Aluminum Split Bolt

*Nsi Industries*

Catalog Number	APS11
Manufacturer	Nsi Industries
Description	Aluminum Dual-Rated Split Bolt 8 Sol - 1/0 STR Aluminum Dual-Rated Split Bolts Are Made From Tin-Plated Aluminum. UI-486B Listed For Aluminum and Copper Conductor Combinations.
Weight per unit	0.0900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum Alloy-Tin Plated
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	8 SOL - 1/0 STR
Wire Type	Class A & B

### Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

### Dimensions and Weight

Size	L=1.920 - W=.750
------	------------------

### Descriptions

Description	1/0 ALUMINUM SPLIT BOLT
extra long description	NSI APS11 Aluminum Split Bolt 1/0
Features	Aluminum Dual-Rated Split Bolt 8 SOL - 1/0 STR Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Long Description	Aluminum Dual-Rated Split Bolt 8 SOL - 1/0 STR Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Product Type	Aluminum Split Bolt 1/0
Special Features	8 SOL-1/0 STR - 20 Pack

### Manufacturer Information

Brand	NSi
GTIN	00662381020536
Manufacturers Part Number	APS11
UPC	662381020536



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type ..... Aluminum Split Bolts .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 0.09 .....

## Uses, Certifications, and Standards

Application ..... Wire Termination .....

environmental conditions ..... 90 C .....

standard ..... UL486B .....

Temperature Rating ..... 90c .....