

AS8	1.240	2.600	4-250MCM, 4-300MCM, 4-350MCM 4-400MCM, 4-450MCM, 4-500MCM 3-350MCM, 3-400MCM, 3-450MCM 3-500MCM, 2-400MCM, 2-450MCM 2-500MCM
AS7	1.010	2.100	4-3/0, 4-4/0, 3-4/0 3-250MCM, 3-300MCM, 2-250MCM 2-300MCM, 2-350MCM, 1-1000MCM
AS6	1.015	1.760	4-1, 4-1/10, 4-2/0, 3-1/0, 3-2/0 3-3/0, 2-2/0, 2-3/0, 2-4/0 1-600MCM, 1-650MCM, 1-700MCM 1-750MCM, 1-800MCM, 1-900MCM
AS5	.875	.890	3-1, 2-1, 2-1/10, 1-300MCM, 1-350MCM 1-400MCM, 1-450MCM, 1-500MCM
AS4	.815	1.250	8/4, 6/2, 6/3 6/4, 4/2, 4/3
AS3	.675	1.020	10/4, 8/2, 8/3, 1/1
AS2	.605	.840	12/4, 10/2, 10/3, 2/1
AS1	.625	.655	14/4, 12/3, 6/1, 4/1
AS0	.568	.652	14/2, 14/3, 12/2
PART No.	"A"	"B"	Wire Ranges

