



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ASK1K1 (1)-2/0 to (1)-2/0 Power Dist Block

*Nsi Industries*

Catalog Number	ASK1K1
Manufacturer	Nsi Industries
Description	Power Distribution Block, 1 Primary Openings, 1 Secondary Openings, #14 to #2/0 Awg Primary Opening Wire Size, #14 to #2/0 Awg Secondary Opening Wire Size, 175 A, 600 V, Clear Acrylic, Maximum Of +90 °C, 2.9 In Overall Length, 1.04 In Overall Width, 2.34 In Overall Height, 0.58 LB
Weight per unit	0.5800 (lbs/each)
Product Category	Power BLKS & Distribution BLKS

### Features

amperage rating	175 Amps Per Pole
Number of Terminals	2
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(1) 2/0-14 AWG(LINE) - (1) 2/0-14 AWG(LOAD)

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Size	L=2.90 - H=2.34 - W=1.04
------	--------------------------

### Descriptions

Description	(1)-2/0 TO (1)-2/0 POWER DIST BLOCK
extra long description	NSI AS-K1-K1 Pwr Dist 1x2/0-14Line
Features	Power Distribution Block (1) 2/0-14 AWG Primary (1) 2/0-14 AWG Secondary Power Distribution Blocks are made of high strength, high-conductivity aluminum alloy and are mounted in a high-strength glass-filled polyester base. Each block can stand alone or combine with other blocks to form a multi-block set.
Special Features	(1) 2/0-14 AWG (Line Side) - (1) 2/0-14 AWG (Load Side) - 175 Amps Per Pole

### Manufacturer Information

GTIN	00662381166043
UPC	662381166043

### Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
Type	Splicer/Reducer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	3
Weight Per each	0.58

## Uses, Certifications, and Standards

Application	NSI
Mounting standard	2 Mounting Holes Recognized to UL1059