



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ATM10 10A 32V DC Fast Acting Mini Blade-Type Fuse

Bussmann Fuses

Catalog Number	ATM10
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Atm Blade Fuse, Color Code Red, 32 VDC, 10A, 1 Kaic, Non Indicating, Blade Fuse, Blade End, Colored Plastic Housing, Zinc Fuse Element
Weight per unit	0.2000 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	10 Amp
connection	Blade End
dimensions	1.4000 IN X 0.3200 IN X 1.5800 IN
interrupt rating	1000 Amp
Material	Colored plastic housing;Zinc fuse element
media	Yes
Voltage Rating	32 VDC

Dimensions and Weight

Size	0.430 In Width X 0.15 In Depth X 0.606 In Height
------	--

Descriptions

Description	10A 32V DC FAST ACTING MINI BLADE-TYPE FUSE
extra long description	BUSS ATM-10 ATM MINI BLADE FUSE - 1
Features	Automotive blade fuses are the industry standard - used in most domestic and imported cars today. All Bussmann series blade fuses meet or exceed OEM and SAE standards. The easyID indicating blade fuses use LED technology making it easier to spot blown fuses in panels tucked in dark locations.
Long Description	Eaton Bussmann series ATM blade fuse, Color code red, 32 Vdc, 10A, 1 kAIC, Non Indicating, Blade fuse, Blade end, Colored plastic housing, zinc fuse element
Product Type	Atm Mini Blade Fuse - 10 Amp (5 In Tin)
Special Features	Color Red

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712814638
Manufacturers Part Number	ATM-10
UPC	051712814638

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Blade fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Vehicles: On-Road
standard	Contact factory, RoHS Compliant