



## B-CAP Wire Connector, B1, Yellow (Jar of 250)



### Product Resources

[B-CAP MSDS](#)  
(PDF | 200K)

[IDEAL Connector UL  
Listed Wire  
Combinations](#)  
(PDF | 378K)

### Features

- Accepts 2 #18 to 3 #12 AWG wire combinations
- Rated for 600 Volt maximum
- Live-action, square-wire spring
- No pre-twisting required
- UL Listed and CSA Certified
- Easily removable for repeat use
- Shell rated for 105° C
- Flame-retardant shell

### Models

Description	Catalog #
B-CAP Wire Connector, B1, Yellow (Jar of 250)	B1-250JR



## B-CAP Wire Connector, B1, Yellow (Jar of 250)



### Product Resources

[B-CAP MSDS](#)  
(PDF | 200K)

[IDEAL Connector UL  
Listed Wire  
Combinations](#)  
(PDF | 378K)

### Features

- Accepts 2 #18 to 3 #12 AWG wire combinations
- Rated for 600 Volt maximum
- Live-action, square-wire spring
- No pre-twisting required
- UL Listed and CSA Certified
- Easily removable for repeat use
- Shell rated for 105° C
- Flame-retardant shell

### Models

Description	Catalog #
B-CAP Wire Connector, B1, Yellow (Jar of 250)	B1-250JR