



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB3070H Bab 3-Pole 70A MCB

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BAB3070H |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 70 A, 10 Kaic, Three-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | 3 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| amperage rating | 70 A |
| dimensions | 3.9000 IN X 3.2000 IN X 4.9000 IN |
| interrupt rating | 10 |
| media | Yes |
| Poles | 3 |
| Trip Type | Non-Interchangeable |
| Voltage Rating | 240 V - 240 V |

Descriptions

| | |
|------------------------|--|
| Description | BAB 3-POLE 70A MCB |
| extra long description | ETN BAB3070H 70A, 3 pole circuit br |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,70 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase |
| Product Type | 70A, 3 Pole Circuit Breaker, Pow-R-Line |
| Special Features | Bolt-on mounting |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton Corp |
| GTIN | 00786679303702 |
| Manufacturers Part Number | BAB3070H |
| UPC | 786679303702 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 8 |
| Weight Per each | 1.05 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| standard | CSA Certified,UL Listed |