



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BC4SS10C 15.6" 50LB #10SCREW Nylon Barb CBL Tie *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | BC4SS10C  |
| Manufacturer     | Panduit Corporation   |
| Description      | Dome-Top® Barb Ty Clamp Tie, Standard Cross Section, #10 (M5) Screw, 15.6 (396MM) Length, Nylon 6.6, Natural, Standard Package. |
| Weight per unit  | 0.8000 (lbs/each)   |
| Product Category | Cable Ties & Wraps  |

### Features

|                  |     |
|------------------|-----|
| media            | Yes |
| Tensile Strength | 50  |

### Dimensions and Weight

|        |      |
|--------|------|
| Length | 15.6 |
| Width  | NA   |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 15.6" 50LB #10SCREW NYLON BARB CBL TIE  |
| extra long description | PAN BC4S-S10-C Dome-Top® BC4S-S10-C   |
| Long Description       | Dome-Top® barb ty clamp tie, standard cross section, #10 (M5) screw, 15.6 (396mm) length, nylon 6.6, natural, standard package. |
| Product Type           | Dome-Top® BC4S-S10-C Cable Tie  |
| Special Features       | Plenum  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Panduit®       |
| GTIN                      | 00074983523306 |
| Manufacturers Part Number | BC4S-S10-C     |
| UPC                       | 074983523306   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
| Type                 | Cable Tie  |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 100 |
| Package         | 500 |
| Weight Per each | 0.8 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | General   |
| standard    | UL 62275 Compliant (Type 2, 21), UL Listed (File #E56854) |