# Specifications



**Photo is representative**

## Eaton BJ44

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG44 HDG, 1-1/4" trade size

### General specifications

| | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series XJG bonding jumper |
| **CATALOG NUMBER** | BJ44 |
| **UPC** | 782274991894 |
| **PRODUCT LENGTH/DEPTH** | 24 in |
| **PRODUCT HEIGHT** | 0.88 in |
| **PRODUCT WIDTH** | 0.19 in |
| **PRODUCT WEIGHT** | 1.4 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **CONDUIT TYPE** | Rigid/IMC |
| **TRADE SIZE** | 1-1/4" |
| **CONDUIT MOVEMENT - MAX** | 4" |
| **SPECIAL FEATURES** | Used with XJG44 HDG |

## Resources

| | |
|---|---|
| **BROCHURES** | Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure |
| **CATALOGS** | Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page |
| **CERTIFICATION REPORTS** | XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification<br>XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification |
| **SPECIFICATIONS AND DATASHEETS** | Expansion and Deflection Couplings<br>Eaton Specification Sheet - BJ44 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

# Specifications



**Photo is representative**

## Eaton BJ44

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG44 HDG, 1-1/4" trade size

### General specifications

| | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series XJG bonding jumper |
| **CATALOG NUMBER** | BJ44 |
| **UPC** | 782274991894 |
| **PRODUCT LENGTH/DEPTH** | 24 in |
| **PRODUCT HEIGHT** | 0.88 in |
| **PRODUCT WIDTH** | 0.19 in |
| **PRODUCT WEIGHT** | 1.4 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **CONDUIT TYPE** | Rigid/IMC |
| **TRADE SIZE** | 1-1/4" |
| **CONDUIT MOVEMENT - MAX** | 4" |
| **SPECIAL FEATURES** | Used with XJG44 HDG |

## Resources

| | |
|---|---|
| **BROCHURES** | Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure |
| **CATALOGS** | Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page |
| **CERTIFICATION REPORTS** | XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification<br>XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification |
| **SPECIFICATIONS AND DATASHEETS** | Expansion and Deflection Couplings<br>Eaton Specification Sheet - BJ44 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.