

Eaton BKHKD400

Catalog Number: BKHKD400

Eaton Pow-R-stock series Main circuit breaker kit, HKD circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 400A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Pow-R-Stock main breaker kit	BKHKD400
UPC	Product Length/Depth
786689030971	5.5 in
Product Height	Product Width
10 in	5.5 in
Product Weight	Certifications
11.5 lb	UL Listed

Product specifications

Circuit breaker type

HKD

Mounting

Top, bottom

Phase

Single-phase, three-phase

Rated operational current

400A

Series

Pow-R-stock

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKHKD400](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BKHKD400

Catalog Number: BKHKD400

Eaton Pow-R-stock series Main circuit breaker kit, HKD circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 400A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Pow-R-Stock main breaker kit	BKHKD400
UPC	Product Length/Depth
786689030971	5.5 in
Product Height	Product Width
10 in	5.5 in
Product Weight	Certifications
11.5 lb	UL Listed

Product specifications

Circuit breaker type

HKD

Mounting

Top, bottom

Phase

Single-phase, three-phase

Rated operational current

400A

Series

Pow-R-stock

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKHKD400](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)