



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1624B100 16/24C 100A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR1624B100
Manufacturer	Eaton Corp
Description	BR Style Load Center, 16 Spaces, 24 Circuits, 100 A, 120/240 V Ac, #4 to 1/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 21 In Overall Height
Weight per unit	22.1 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	100 WTT
Box Size	08447
cover	Cover included
Cover Type	Cover included
dimensions	95.2500millimetreX28.5750centimetreX38.1000centimetre
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	08447
------	-------

Descriptions

Description	16/24C 100A 1PH MB LOADCENTER
extra long description	ETN BR1624B100 BR style 1-inch load

Manufacturer Information

GTIN	00786676444057
UPC	786676444057

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	Main circuit breaker
unspsc code	39121101



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 22.1

Uses, Certifications, and Standards

Enclosure NEMA 1

Mounting Combination

standard UL 67;UL 50