

Eaton BR2020B100

Catalog Number: BR2020B100

Eaton BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 20-pole, 20 circuits, 20 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c2 box size



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR2020B100
UPC	Product Length/Depth
786676444156	24.75 in
Product Height	Product Width
4.25 in	16 in
Product Weight	Warranty
23.49 lb	10 year
Certifications	
UL 67	
UL 50	

Product specifications

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

20

Number of spaces

20

Phase

Single-phase

Wire size

#4-1/0 AWG Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

C2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BR2020B100

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)