Specifications







Eaton BR2024B125

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 125A, single-phase, 24-pole, 24 circuits, 20 spaces, 120/240V, #4-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size

General specifications	
PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR2024B125
UPC	786676444453
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	16.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	24 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Product specifications	
SPECIAL FEATURES	No feed-thru lugs
ТҮРЕ	Main circuit breaker
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	20
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG Cu/Al
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	C1
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR2024B125
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







