



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2024B125R 1PH 125A 10KAIC MCB 20/24 Cir. Al Bus Nema3r

Eaton Corp

Catalog Number	BR2024B125R
Manufacturer	Eaton Corp
Description	BR Style Load Center, 20 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #4 to 2/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 5.19 In Overall Width, 25 In Overall Height
Weight per unit	5.5 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	125
Cover Type	Cover included
dimensions	27.0000 IN X 15.5000 IN X 5.5000 IN
max amps	125
max poles/spaces	20/24
Phase	1

Dimensions and Weight

Depth	27
Height	5.5
Size	C3r
Width	15.5

Descriptions

Description	1PH 125A 10KAIC MCB 20/24 CIR. AL BUS NEMA3R
extra long description	ETN BR2024B125R 1Ph/BR LC125A 10kAI

Manufacturer Information

GTIN	00786676444507
UPC	786676444507

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	5.5

Uses, Certifications, and Standards

standard	UL 67,UL 50
----------	-------------