



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2040B100

UPC:782116904365

Dimensions:

- **Height:** 25 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BW
- **Number Of Circuits:** 40
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, BR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR2040B100](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2040B100

UPC:782116904365

Dimensions:

- **Height:** 25 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BW
- **Number Of Circuits:** 40
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, BR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR2040B100](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.