

Specifications



Eaton BR2040B200R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 40-pole, 40 circuits, 20 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, d1r box size

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR2040B200R
UPC	786676445757
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	21 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	35.13 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	No feed-thru lugs
TYPE	Main circuit breaker
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	20
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil Cu/Al
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	D1R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR2040B200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

