

Specifications



Eaton BR2040L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, C3R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, 40 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR2040L200R
UPC	786676447553
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Has notch for brhdk125 hold-down kit.



Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	200 A

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
----------	----------------------------------------------------------------------------------------------------

BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	C3R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR2040L200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton BR2040L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, C3R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, 40 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR2040L200R
UPC	786676447553
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Has notch for brhdk125 hold-down kit.



Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	200 A

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
----------	----------------------------------------------------------------------------------------------------

BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	C3R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR2040L200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

