

Eaton BR2040L200R

Catalog Number: BR2040L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, C3R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, 40 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR2040L200R
UPC	Product Length/Depth
786676447553	5.19 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
15.5 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Has notch for brhdk125 hold-down kit.

Product specifications

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

C3R

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR2040L200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)