

Eaton BR2040LQN125RG

Catalog Number: BR2040LQN125RG

Eaton BR main lug loadcenter, 125 A,C1R,Aluminum, NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,40 Circuits,Twenty-four pole,20 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#6-2/0 AWG Cu/Al

General specifications



Product Name	Catalog Number
Eaton BR main lug loadcenter	BR2040LQN125RG
UPC	Product Length/Depth
786685953588	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
24.3 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

40

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

C1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Specifications and datasheets

Eaton Specification Sheet - BR2040LQN125RG

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)