



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR2040N200RG**

**UPC:**782116893911

### Dimensions:

- **Height:** 21 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Ground bar
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** D1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 40
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

### Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



### Instructions

- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR2040N200RG](#)

### **Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR2040N200RG**

**UPC:**782116893911

### Dimensions:

- **Height:** 21 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Ground bar
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** D1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 40
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

### Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



### Instructions

- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR2040N200RG](#)

### **Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.