



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BR20I RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv** *Hubbell Wiring Devices*

Catalog Number	BR20I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Weight per unit	0.0430 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	9000
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### **Dimensions and Weight**

Size	1.32 in x 0.83 in x 3.28 in
------	-----------------------------

### **Descriptions**

Description	RCPT, DUP SB, COM GRD, 20A 125V, B/S, IV
extra long description	HWK BR20I RCPT, DUP SB, COM GRD, 2
Long Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Product Type	RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv
Special Features	Self Grounding

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585834887
Manufacturers Part Number	BR20I
series	Commercial Specification Grade
UPC	783585834887



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Standard Duplex

## Packaging

Carton	10
Weight Per each	0.043

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA 22.2, No. 42;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186