



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR20I RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv *Hubbell Wiring Devices*

Catalog Number	BR20I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Weight per unit	0.1900 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3
pallet quantity	9000
Phase	1
Poles	2
Voltage Rating	125 V
Wattage	2,500
Wire Size	#12 to #10

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Size	1.32 in x 0.83 in x 3.28 in
------	-----------------------------

Descriptions

Description	RCPT, DUP SB, COM GRD, 20A 125V, B/S, IV
extra long description	HWK BR20I RCPT, DUP SB, COM GRD, 2
Long Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Product Type	RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv
Special Features	Self Grounding



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585834887
Manufacturers Part Number	BR20I
series	Commercial Specification Grade
UPC	783585834887

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Standard Duplex

Packaging

Carton	10
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA 22.2, No. 42;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186