



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR20WHIWRTR WTR/Tamp, Com GRD, 20A 125V, 5-20R, WH *Hubbell Wiring Devices*

Catalog Number	BR20WHIWRTR
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Tamper and Weather-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Weight per unit	0.0450 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	8500
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### Dimensions and Weight

Size	Standard Sized Product
------	------------------------

### Descriptions

Description	WTR/TAMP, COM GRD, 20A 125V, 5-20R, WH
extra long description	HWK BR20WHIWRTR WTR/TAMP, COM GRD,
Long Description	Straight Blade Devices, Receptacles, Tamper and Weather-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Product Type	WTR/Tamp, Com GRD, 20A 125V, 5-20R, WH
Special Features	Tamper and Weather Resistant- Self Grounding

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585144726
Manufacturers Part Number	BR20WHIWRTR
series	Commercial Specification Grade
UPC	783585144726



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Tamper-Resistant, Weather Resistant

## Packaging

Carton	1
Package	10
Weight Per each	0.045

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Weather resistant
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186