



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2424L125 24/24C 125A 1PH Mlo Loadcenter

Eaton Corp

Catalog Number	BR2424L125
Manufacturer	Eaton Corp
Description	Main Lug Load Center, 24 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #6 to 2/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 23 In Overall Height
Weight per unit	24.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	125 VAC
Box Size	QUARTZ LIGHTING LENS, GLASS LENS REFRACTOR/LENS TYPE; QF500F QUARTZ FLOODLIGHT FIXTURE TYPE; RAB[R] BRAND
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX58.4200centimetre
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	C2
------	----

Descriptions

Also Known As...	panel board Fuse box load center electric panel panelboard breaker panel breaker box panel
Description	24/24C 125A 1PH MLO LOADCENTER
extra long description	ETN BR2424L125 BR style 1-inch load

Manufacturer Information

GTIN	00786676447102
UPC	786676447102



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50