



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2430L125G 125A 1PH LD-CTR 24/30C Nema1

Eaton Corp

Catalog Number	BR2430L125G
Manufacturer	Eaton Corp
Description	Eaton BR Style 1-Inch Loadcenter, Main Lug, Ground Bar, 125A, Single-Phase, 30-Pole, 30 Circuits, 24 Spaces, 120/240V, 2/0-#14 Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, G1 Box Size
Weight per unit	24.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	125 VAC
Box Size	M104D-731
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX68.5800centimetre
interrupt rating	10 kAIC
main circuit breaker	Environmental Conditions Wet Location; Includes Ground Screw; Shape Round
Number of Circuits	30 W
number of spaces	24 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#2/0-300 kcmil Cu/Al at 60°C or 75°C

Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

Dimensions and Weight

Size	M104D-731
------	-----------

Descriptions

Description	125A 1PH LD-CTR 24/30C NEMA1
extra long description	ETN BR2430L125G BR style 1-inch loa
Long Description	Eaton BR style 1-inch loadcenter, main lug, ground bar, 125A, single-phase, 30-pole, 30 circuits, 24 spaces, 120/240V, 2/0-#14 Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, g1 box size
Product Type	BR Style 1-Inch Loadcenter
Special Features	Ground bar



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00782116139293
Manufacturers Part Number	BR2430L125G
UPC	782116139293

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50