



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR3030B150 30/30C 150A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR3030B150
Manufacturer	Eaton Corp
Description	BR Style Load Center, 30 Spaces, 30 Circuits, 150 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 34.13 In Overall Height
Weight per unit	34.9 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	150 WTT
Box Size	G1r
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX53.3400centimetre
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
max amps	150
max spaces/poles	30
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	G1r
------	-----

Descriptions

Description	30/30C 150A 1PH MB LOADCENTER
extra long description	ETN BR3030B150 BR style 1-inch load

Manufacturer Information

GTIN	00786676445054
sub brand	None IN
UPC	786676445054



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Packaging

Carton	1
Weight Per each	34.89

Uses, Certifications, and Standards

Enclosure	NEMA 1
Mounting	Combination
standard	UL 67; UL 50