



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3030BC100

UPC:786676001175

Dimensions:

- **Height:** 21 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:36 LB

Notes:Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** C1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:



- Dimensional Drawing - BR 1 LOADCENTER, BR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE
- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR3030BC100

Certifications:

- UL 67
- UL 50

Product compliance: No Data



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3030BC100

UPC:786676001175

Dimensions:

- **Height:** 21 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:36 LB

Notes:Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** C1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:



- Dimensional Drawing - BR 1 LOADCENTER, BR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE
- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR3030BC100

Certifications:

- UL 67
- UL 50

Product compliance: No Data