



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR3040B200 30/40C 200A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR3040B200
Manufacturer	Eaton Corp
Description	BR Style Load Center, 30 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 5.19 In Overall Width, 25 In Overall Height
Weight per unit	34.9 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	59120
Box Size	C3r
cover	Cover included
Cover Type	Cover included
dimensions	5.1900 IN X 14.3100 IN X 25.0000 IN
main circuit breaker	BWH
max amps	200
max spaces/poles	30/40
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	C3r
------	-----

Descriptions

Description	30/40C 200A 1PH MB LOADCENTER
extra long description	ETN BR3040B200 BR style 1-inch load

Manufacturer Information

GTIN	00786676445955
UPC	786676445955



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Packaging

Carton	1
Weight Per each	34.87

Uses, Certifications, and Standards

Enclosure	NEMA 3R
standard	UL 67;UL 50