

Specifications



Eaton BR3040B200R

Value pack, Main circuit breaker loadcenter, 200A, C3, Aluminum, Interlock cover, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3040B200R
UPC	786676446051
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	43 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Value pack
TYPE	Main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Interlock cover
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil Cu/Al
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	C3
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3040B200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton BR3040B200R

Value pack, Main circuit breaker loadcenter, 200A, C3, Aluminum, Interlock cover, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3040B200R
UPC	786676446051
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	43 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Value pack
TYPE	Main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Interlock cover
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil Cu/Al
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	C3
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3040B200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

