



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR3040B200V4 30/40C 200A 1PH MB Loadcenter Value Pack

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BR3040B200V4 |
| Manufacturer | Eaton Corp |
| Description | BR Style Load Center, 30 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material |
| Weight per unit | 37.2 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|----------------------|---|
| amperage rating | 59120 |
| Box Size | QUARTZ LIGHTING LENS, GLASS LENS REFRACTOR/LENS TYPE; QF500F QUARTZ FLOODLIGHT FIXTURE TYPE; RAB[R] BRAND |
| cover | Cover included |
| Cover Type | Cover included |
| dimensions | 98.5520millimetreX36.3474centimetreX58.4200centimetre |
| main circuit breaker | BWH |
| number of spaces | 30 W |
| Number of Wires | Three-wire |
| Phase | 1 W |
| used with | Type BR 1-inch breakers |

Material, Color, and Finish

| | |
|--------------------|----------|
| Enclosure Material | Metallic |
|--------------------|----------|

Dimensions and Weight

| | |
|------|----|
| Size | C2 |
|------|----|

Descriptions

| | |
|------------------------|---|
| Also Known As... | Fuse box load center panel board breaker panel panel panelboard breaker box electric panel |
| Description | 30/40C 200A 1PH MB LOADCENTER VALUE PACK |
| extra long description | ETN BR3040B200V4 BR style 1-inch lo |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00782113491653 |
| UPC | 782113491653 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | Main circuit breaker |
| unspsc code | 39121101 |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 37.18 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| Enclosure | NEMA 1 |
| Mounting | Combination |
| standard | UL 67;UL 50 |