

Eaton BR3040N200R

Catalog Number: BR3040N200R

Eaton BR convertible loadcenter, Value pack, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR3040N200R
UPC	Product Length/Depth
786676448901	5.19 in
Product Height	Product Width
34 in	14.31 in
Product Weight	Warranty
40 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Product specifications

Special features

Value pack

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

Eaton Specification Sheet - BR3040N200R

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BR3040N200R

Catalog Number: BR3040N200R

Eaton BR convertible loadcenter, Value pack, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR3040N200R
UPC	Product Length/Depth
786676448901	5.19 in
Product Height	Product Width
34 in	14.31 in
Product Weight	Warranty
40 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Product specifications

Special features

Value pack

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR3040N200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)